

00200000 & 00200300 CONNECTORS

ABS/EBS ADR Cables • Polyurethane sheath material



00200000 ABS
00200200 EBS



00200100 ABS
00200300 EBS

Description

ABS/EBS ADR cable resists UV-ray and low temperatures, as well as being resistant to oil, weathering and chemicals thanks to the PUR sheathing. In addition they provide for higher resistance against wear, abrasion, microbiotic attack and hydrolysis. The cables have been produced in accordance with the latest international standards ISO 4141 and ISO 6722.

Features and Benefits

- Standards: Conforms to ISO 4141 & ISO 6722 recommendations and standards.
- Wire insulation and inner sheath: PVC
- Sheath: PUR
- Min/Max temperatures: -40°C / +85°C.

Specifications Overview

Voltage:	12V/24V
Standards:	ISO 4041 ISO 6722

Web Resources

Download technical resources at:
littelfuse.com/connectors

Ordering Information

PART NUMBER	MATERIAL	NUMBER AND SECTION OF WIRES	EXTERNAL DIAMETER	ROLL	APPLICATION
00200000	Polyurethane	2x4 mm ² + 3x1,5 mm ²	11,5 mm	50 m	ABS
00200100	Polyurethane	2x4 mm ² + 3x1,5 mm ²	11,5 mm	500 m	ABS
00200200	Polyurethane	2x4 mm ² + 1x(2x1,5) mm ²	13,5 mm	50 m	EBS
00200300	Polyurethane	2x4 mm ² + 1x(2x1,5) mm ²	13,5 mm	500 m	EBS