


ISO MINI RELAYS SERIES

18 V AND 36 V MAX ISO MINI 6.3 MM FORM A, FORM 2A,
AND FORM C RELAYS



R2-400112-RN

RC-400112-NN

Description

Our ISO Mini Relays are compact, modular, general-purpose relays that allow you to tailor your vehicle's power distribution box for the capability you need, including lighting, starting, horn, heating and cooling, or fan control.

Adhering to the ISO Mini 6.3 mm form factor, these relays plug into existing, ISO Mini boxes along with fuses or other components (sold separately).

This series offers a wide selection of Mini relays to meet the requirements of a variety of applications. Options include Form A (SPST), Form 2A (SPST with two terminals), and Form C (SPDT) relays, versions with resistor suppression, diode suppression, or no suppression, and models that are sealed (IP64), unbracketed or unsealed (IP40), bracketed configurations.

Web Resources

Download 2D print, installation guide and technical resources at: littelfuse.com/ISO-MINI

Specifications

Current Rating Continuous:	20 ADC, 40 ADC
Max Voltage Rating:	36 VDC, 18 VDC
Ingress Protection:	IP-40, IP-64
Mounting Method:	Panel Mount
Coil Voltage:	12 VDC, 24 VDC
Coil Impedance:	90 $\Omega \pm 10\%$, 360 $\Omega \pm 10\%$
Contacts:	Silver Alloy
Input Terminals:	Tin-Plated
Output Terminals:	Tin-Plated
Temperature:	-40°C to 85°C
Circuitry:	SPST
Housing:	Black Plastic Body
Voltage Drop:	30m Ω Max
Insulation Resistance:	100M Ω Min

Applications

- Lighting Control
- Starting Control
- Horn Control
- Heating and Cooling Control
- Fan Control

Features and Benefits

- Broad offering of Form A (SPST), Form 2A (SPST with two terminals), and Form C (SPDT) relay options
- Rated for either 18 V max with a 12 V dc coil rating or 36 V max with a 24 V dc coil rating
- Versions are available with either a 20 A or 40 A continuous current rating
- Suppression options include resistor, diode, and no suppression
- Sealed (IP64) and unsealed (IP40) versions to match the water- and dust-protection requirements of your application
- Bracketed options are available for panel mounting

ISO MINI RELAYS SERIES

18 V AND 36 V MAX ISO MINI 6.3 MM FORM A, FORM 2A,
AND FORM C RELAYS

Ordering Information

PART NUMBER	DESCRIPTION	COIL TYPE	MOUNTING METHOD
R2-400112-RN	18 V Max 40 A Form 2A ISO Mini Relay with Resistor Suppression and Bracket	Isolated W/ Resistor Suppression	BRACKET STYLE "L" With Hole Diameter of 0.209" (5.3 MM)
R2-400112-RN-BX	18 V Max 40 A Form 2A ISO Mini Relay with Resistor Suppression and Bracket - Boxed	Isolated W/ Resistor Suppression	BRACKET STYLE "L" With Hole Diameter of 0.209" (5.3 MM)
RA-200024-DS	36 V Max 20 A Sealed Form A ISO Mini Relay with Diode Suppression	Isolated W/ Diode Suppression	Blade Terminals Mounting
RA-400112-DN	18 V Max 40 A Form A ISO Mini Relay with Diode Suppression and Bracket	Isolated W/ Diode Suppression	BRACKET STYLE "L" With Hole Diameter of 0.209" (5.3 MM)
RA-400112-DN-BX	18 V Max 40 A Form A ISO Mini Relay with Diode Suppression and Bracket - Boxed	Isolated W/ Diode Suppression	BRACKET STYLE "L" With Hole Diameter of 0.209" (5.3 MM)
RA-400112-NN	18 V Max 40 A Form A ISO Mini Relay with Bracket	Isolated	BRACKET STYLE "L" With Hole Diameter of 0.209" (5.3 MM)
RA-400112-NN-BX	18 V Max 40 A Form A ISO Mini Relay with Bracket - Boxed	Isolated	BRACKET STYLE "L" With Hole Diameter of 0.209" (5.3 MM)
RA-400112-RN	18 V Max 40 A Form A ISO Mini Relay with Resistor Suppression and Bracket	Isolated W/ Resistor Suppression	BRACKET STYLE "L" With Hole Diameter of 0.209" (5.3 MM)
RA-400112-RN-BX	18 V Max 40 A Form A ISO Mini Relay with Resistor Suppression and Bracket - Boxed	Isolated W/ Resistor Suppression	BRACKET STYLE "L" With Hole Diameter of 0.209" (5.3 MM)
RC-200124-DN	36 V Max 20 A Form C ISO Mini Relay with Diode Suppression and Bracket	Isolated W/ Diode Suppression	BRACKET STYLE "L" With Hole Diameter of 0.209" (5.3 MM)
RC-200124-DN-BX	36 V Max 20 A Form C ISO Mini Relay with Diode Suppression and Bracket - Boxed	Isolated W/ Diode Suppression	BRACKET STYLE "L" With Hole Diameter of 0.209" (5.3 MM)
RC-200124-NN	36 V Max 20 A Form C ISO Mini Relay with Bracket	Isolated	BRACKET STYLE "L" With Hole Diameter of 0.209" (5.3 MM)
RC-200124-NN-BX	36 V Max 20 A Form C ISO Mini Relay with Bracket - Boxed	Isolated	BRACKET STYLE "L" With Hole Diameter of 0.209" (5.3 MM)
RC-200124-RN	36 V Max 20 A Form C ISO Mini Relay with Resistor Suppression and Bracket	Isolated W/ Resistor Suppression	BRACKET STYLE "L" With Hole Diameter of 0.209" (5.3 MM)
RC-200124-RN-BX	36 V Max 20 A Form C ISO Mini Relay with Resistor Suppression and Bracket	Isolated W/ Resistor Suppression	BRACKET STYLE "L" With Hole Diameter of 0.209" (5.3 MM)
RC-400012-DS	18 V Max 40 A Sealed Form C ISO Mini Relay with Diode Suppression	Isolated W/ Diode Suppression	Blade Terminals Mounting
RC-400012-DS-BX	18 V Max 40 A Sealed Form C ISO Mini Relay with Diode Suppression - Boxed	Isolated W/ Diode Suppression	Blade Terminals Mounting
RC-400112-DN	18 V Max 40 A Form C ISO Mini Relay with Diode Suppression and Bracket	Isolated W/ Diode Suppression	BRACKET STYLE "L" With Hole Diameter of 0.209" (5.3 MM)
RC-400112-DN-BX	18 V Max 40 A Form C ISO Mini Relay with Diode Suppression and Bracket - Boxed	Isolated W/ Diode Suppression	BRACKET STYLE "L" With Hole Diameter of 0.209" (5.3 MM)
RC-400112-NN	18 V Max 40 A Form C ISO Mini Relay with Bracket	Isolated	BRACKET STYLE "L" With Hole Diameter of 0.209" (5.3 MM)
RC-400112-NN-BX	18 V Max 40 A Form C ISO Mini Relay with Bracket - Boxed	Isolated	BRACKET STYLE "L" With Hole Diameter of 0.209" (5.3 MM)
RC-400112-RN	18 V Max 40 A Form C ISO Mini Relay with Resistor Suppression and Bracket	Isolated W/ Resistor Suppression	BRACKET STYLE "L" With Hole Diameter of 0.209" (5.3 MM)
RC-400112-RN-BX	18 V Max 40 A Form C ISO Mini Relay with Resistor Suppression and Bracket - Boxed	Isolated W/ Resistor Suppression	BRACKET STYLE "L" With Hole Diameter of 0.209" (5.3 MM)
RA-200124-DN	36 V Max 20 A Form A ISO Mini Relay with Diode Suppression and Bracket	Isolated W/ Diode Suppression	BRACKET STYLE "L" With Hole Diameter of 0.209" (5.3 MM)
RC-200024-DS	36 V Max 20 A Sealed Form C ISO Mini Relay with Diode Suppression	Isolated W/ Diode Suppression	Blade Terminals Mounting