


COLE-HERSEE CO.

APPLICABLE SAE STANDARD OR RECOMMENDED PRACTICE SAE J259



RATINGS AT 12 V D.C.	
ACC. CIRCUIT	10 AMPS
IGN.	10

*83357 HENCOL KEY (2 KEYS RINGED)

956-6307

*83348 FACE NUT, ALUMINUM

3/4-24 UNS 2A THD.



CASE (3), ZINC DIE CAST

GASKET, VELLUMOID (NOTE *2)

TERMINAL INSULATOR MOLDED DUREZ (NOTE *2)

SCREW 1/8-20
LOCKWASHER,
3 REQ'D

1/8 DRAIN HOLE
O RING (NOTE *1)



NOTE:

1. SHAFT "O" RING SEALED TO CASE
2. TERMINAL INSULATOR GASKET SEALED
- 3 ALL STEEL PARTS PLATED

REV	WAS	DATE	BY	REV	WAS	DATE	BY	MATERIAL	DRAWN	CHECKED	APPROVED	SCALE	USED ON	DATE DRAWD
				D	ECN COPY	3/2/88	MA		CF	UM		FULL		1-31-67
				C	NOTE 3 ADDED	12/18/92	JK	FINISH	COLE-HERSEE COMPANY BOSTON 27, MASS., U.S.A.					DATE DRAWD
				B	HOUSING	8-17-82	PK							
				A	SPEC ADDED	3-4-74	W	TOLERANCES FRACTIONAL + DECIMAL +	NAME	ACC-IGNITION SWITCH				PART NO
					ISSUED	3-9-67	HF						956-6307	