


LIQUID LEVEL PROBES & PROBE HOLDERS

LIQUID LEVEL CONTROL ELECTRODES		
Product	Features	Accessory For
LLP-24 Liquid Level Probe	 Threaded stainless steel probe measuring 24 in. (61 cm) long. Designed for use with PHST-38QTN liquid level control electrodes.	PHST-38QTN
PHST-38QTN Probe Holder P0700-409 Protective Boot	  Designed for use with all conductive liquid level controls. Composed of insulators and metal parts made of number 300 series stainless steel. These internally conductive probe holders are designed for a maximum steam pressure of 240 PSI; 400° F maximum. Maximum voltage from electrode to ground. PHST-38QTN is UL 353 Recognized.	Series: LLC1 LLC2 LLC4 LLC5 LLC6 LLC8 PC-XXX-LLC-CZ PC-XXX-LLC-GM 460-15-100-LLS