

Fuse Type	Fuse series	HOLDER TYPE				
		Panel Mount	Blocks	PC Board	Clips	In-Line
2AG (5 x 15 mm)	225	3452 International Shock-Safe	254 Omni-Blok	254101	111501	150274
	229	345 International Shock-Safe (old)		254121 Beryllium Copper	111505 Beryllium Copper	
		245001 Shorty Solder QC			111506 Beryllium Copper	
		245002 Shorty NEMA QC				
		286377 Flip-Top				
3AG (6.3 x 32mm)	312	3453 International Shock-Safe	354 Omni-Blok	345101 horizontal	102071	155100 Twist-Lock
	313	345 International Shock-Safe (old)	356 Screw terminal	810 horizontal	102074	150215 Assem., no fuse
	314	342 Traditional	359 Screw terminal	862 horizontal	122083	
	326	344 Indicating Snap Mount		811 vertical	122087 Beryllium Copper	155000 Heavy Duty
		348 Snap Mount			122088	150079 Assem., no fuse
		346877 Flip-Top			122093 Beryllium Copper	
		342006 Watertight screw-in			102078	
		340312/3 Shielded Watertight			102079	
		342024 Mil high temp knurled			102076	
		342025 Mil high temp fluted			102080	
		800 2.5 Watt			122090 Beryllium Copper	
		80001 500V 2.5 Watt			12100 Beryllium Copper	
		860 4 Watt			100058	
					101001	
					101002	
				101003		
				102064		
				121004 Beryllium Copper		
				121002 Beryllium Copper		
				518 Combo, 3AG & 5x20		
5 x 20 mm	213 215	3455 International Shock-Safe	520003 Omni-Blok QC	345121 horizontal	111501	150274
	216 217	345 International Shock-Safe (old)	520004 Omni-Blok Solder	520101 Omni-Blok	445001	
	218 219A	286677 Flip-Top	520005 Omni-Blok anti-rotation	OPTF0060W no cover option	111505 Beryllium Copper	
	232 233	800		OPTF0075P cover optional	30210	
	234 235	820		00BS0232P cover	111506 Beryllium Copper	
	239	823 snap-in		646	520001	
		821		648 cover	100054	
		850		640 cover and puller combo	100056	
		851		649	111005 T&R	
		860 4 Watt		656 659, 660 cover	519 T&R	
		870 medical, captive cap		658 Surface Mt. 659, 660 cover	520	
				810 horizontal	521	
				830 horizontal	518 Combo, 3AG & 5x20	
				862 horizontal		
			811 vertical			
			831 vertical 4 pin			
			834 vertical			
			852 vertical 2 pin			

continued on next page

Fuse Type	Fuse series	HOLDER TYPE				
		Panel Mount	Blocks	PC Board	Clips	In-Line
5 x 20 mm <i>(continued)</i>				853 vertical 2 pin 860 4 Watt		
TR5® fuse	370, 372 373, 378 374, 379 375, 382 384	570 575 cap		559 560 562 564 Surface mt 565 90° 571 575 cap		
Alarm	481	482 ZXP		482 ZXB		
ATO® fuse	257 TAC FKS, OF2 TF	155320U 14AWG, unassembled 155300 14AWG, 8" loop 155430U 10AWG, unassembled 155400 10AWG, 8" loop	350417 5 position side mt. 350418 5 position bottom mt.	445715 FLR 42V FLR 80V	100057	FHAC001 16AWG, 20A FHAC002 12AWG, 30A FH2 80V FKH 58V FK Crimp
MINI® fuse	297, 997 FUN FK1 OF1			153007, 153031 Horizontal 153008, 053032 Vert. End 153009, 155033 Vert. Stackable FL1 125V Vert. Stackable		FHM001 14AWG, 20A FHM002 12AWG, 30A 153002 153003
MAXI™ fuse	299, 999 TOE, FK3 OF3		152001 with screws 152900 Cover			MAH001 6AWG, 60A 152 Splash Proof
MEGA® fuse	298 BF2		2981001 1 position. Many options			FH3 80V
MIDI® fuse	498 BF1		498900 1 position. Many options			
Micro™ fuse	272 273 262 268 269 274 279	281001 Front mt. Neoprene 281007 Front mt. Conductive 282002 Rear mt. Neoprene 282008 Rear mt. Conductive 280003 125V indicating 280004 32V indicating		281005 Vertical silver 281007 Horizontal silver 281008 Vertical tin 281010 Horizontal tin		
Midget	BLF BLN BLS FLA FLM FLQ KLK KDK	571 Standard & Watertight	L60030M	105003 125003 Beryllium Copper	105001 125001 Beryllium Copper 105002 125002 Beryllium Copper	LEB watertight
Class CC	CCMR KLDR KLKR	571CC Standard & Watertight	L60030C			LEC watertight