

150 Series

In-Line Fuseholders for 2AG or 5×20mm Fuses



Product Characteristics

Compatible Fuses	2AG or 5×20mm
Electrical	Maximum current ratings are 5 amperes at 350V for the 2AG size fuses and 10 amperes at 350V for the 5 × 20mm size fuses.**
Body	Black Nylon, UL94 V-0
Terminals	Brass
Wire	16 Awg size; Nominal o.d. 0.104"; color Red
Lead Pull Test	Will withstand 10 lb. pull.
Ambient Temperature	-40°C to +80°C*

Notes:* Refer to [Fuseology](#) for information on proper fuseholder re-rating.

** If use above 32V, power must be turn off when changing the fuse.

Additional Information



Resources



Accessories



Samples

Ordering Information

Ordering Number	Packaging
01500274Z	Bulk Pack (100 Pcs)
01500274LXN	Bulk Pack (50 Pcs)
*01500274ZXU	Bulk Pack (5000 Pcs)

Notes:



* For unassembled Fuseholder, UL Recognition does not apply and is not supplied with wires.

** Images are illustrative

Agency Approval

Agency	Agency File Number
	E14721

Dimensions [mm]

**Warning:** Electrical Shock. Power must be disconnected prior to handling fuse.**Disclaimer Notice** - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at: www.littelfuse.com/disclaimer-electronics.