

# RELAY SOCKETS



99025 Socket



99026 Socket

## Description

Available as Form A (SPST) or Form C (changeover SPDT), with no suppressor / resistor suppressor / diode suppressor, sealed or unsealed.

## Features and Benefits

- Sockets dovetail together.
- Accepts standard quick connect terminals.
- Accept Littelfuse Heavy Duty and High Power Relays & standard ISO relays.
- Bracket for easy mounting.
- Rugged glass-filled polyamide.
- Weatherproof construction.
- Temperature range -40 °C to 85 °C

## Heavy Duty and High Power Relays



| HEAVY DUTY RELAYS |         |
|-------------------|---------|
| RELAY             | VOLTAGE |
| NO 40A            | 12V DC  |
| NC 30A            | 12V DC  |
| NO 20A            | 24V DC  |
| NC 15A            | 24V DC  |

## Applications

- 99025 - Use with Tyco (AMP) terminals 280756 or 280755
- 99026 - Use with Tyco (AMP) terminals 42281 or Ark-Les 3000H112A series

## Web Resources

Download technical resources at:  
[littelfuse.com/RelaySockets](http://littelfuse.com/RelaySockets)

## Ordering Information

| PART NUMBER | DESCRIPTION                                                |
|-------------|------------------------------------------------------------|
| 99025       | Use with High Power Relays, Form A (SPST)                  |
| 99026       | Use with Heavy Duty Relays, Form A (SPST) or Form C (SPDT) |

| HIGH POWER RELAYS |         |
|-------------------|---------|
| RELAY             | VOLTAGE |
| NO 70A            | 12V DC  |
| NC 60A            | 12V DC  |
| NO 35A            | 24V DC  |
| NC 30A            | 24V DC  |

**Datasheet Replaces Hotfeed Number D-600**