

00200800 & 00201500 CONNECTORS

7 and 13-Pole ADR Cables • Polyurethane sheath material



00200800-7 pole
00201400-13 pole



00200900-7 pole
00201500-13 pole

Description

ADR cable resist UV-ray and low temperatures, as well as being resistant to oil, weathering and chemicals thanks to the PUR sheathing. In addition they provide for higher resistance against wear, abrasion, microbiotic attack and hydrolysis. The cables have been produced in accordance with the latest international standards ISO 4041 and ISO 6722..

Features and Benefits

- Standards: Conforms to ISO 4041 & ISO 6722 recommendations and standards.
- Wire insulation and inner sheath: PVC
- Sheath: PUR
- Min/Max temperatures: -40°C / +85°C.

Specifications Overview

Voltage:	12V/24V
Standards:	ISO 4041 ISO 6722

Web Resources

Download technical resources at:
littelfuse.com/connectors

Ordering Information

PART NUMBER	MATERIAL	NUMBER AND SECTION OF WIRES	EXTERNAL DIAMETER	ROLL	APPLICATION
00200800	Polyurethane	6x1 mm + 1x2 mm	9,8 mm	50 m	7 pole
00200900				500 m	
00201400	Polyurethane	3x2,5 mm + 10x1,5 mm	13,5 mm	50 m	13 pole
00201500				500 m	