



**NOTES:**

1. MATERIAL:  
 BASE: UL94V-0 GLASS FILLED NYLON  
 STUDS: M5  
 NUTS: ZINC-PLATED NYLOCK NUT
2. TORQUE RATING: 5±1 Nm
3. FUSE RATING: 30-200A
4. WIRE SIZE: 14-4 AWG (2.5mm<sup>2</sup>-20mm<sup>2</sup>)
5. TEMPERATURE RATING: -40°C TO 125°C

**PACKAGING NOTES:**

1. PARTS ARE PACKED 50 PC PER BAG, 10 BAGS PER BOX.

METRIC  
ASSEMBLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [ ] ARE INCHES

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.



CPK



ST

CP

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL				
	MTRL SPEC			
COPIES TO	1	9	18	
	2	10	19	
	3	12	20	
	4	13	21	
	5	14	23	
	6	15	33	
	7	16	43	
	8	17	53	
	TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-mK)			
	DIMENSION	UP TO 0.5	UP TO 3	UP TO OVER 6
		±0.1	±0.2	±0.3
	TOLERANCE			
	3RD ANGLE PROJECTION			
TITLE    BASE FOR MIDI INLINE HOLDER, W/M5 BOLTS    REVISION    DRWG. NO.    OUTLINE A    OL-498921-2				

LTR	DATE	REVISION	CHK	APD
A	05/16/11	502090ERA-RELEASE	OPL	

