




59024-13

MM	IN
6.85	.270
13.30	.524
13.46	.530
19.05	.750
33.52	1.320
39.14	1.541



- NOTES:
1. SILVERED CONTACTS.
  2. ALL STEEL PARTS PLATED.
  3. 25 AMPS @ 12 V.D.C.
  4. FACE NUT ASSEMBLED

METRIC

DO NOT SCALE

LET	WAS	DATE	BY	LET	WAS	DATE	BY	MATERIAL	DRAWN	CHECKED	APPROV'D	SCALE	DATE DRAWN
								—#—	VAK			1:1	3/25/86
								FINISH					DATE BLUEPRINT
								TOLERANCES	 <b>SW. TOGGLE S.P.D.T.</b>				59024-13
							DECIMAL ±						
								METRIC ±					

BRUN: VG 40-21 63765

EX21032B

CH-188(4-78)