



- NOTES:
 1. MATERIAL: SILICON RUBBER
 2. YELLOW COLOR
 3. 30 DURE HARD \odot

METRIC
COMPONENT

																A	LTR
																504799ERA NEW RELEASED E/JIN	REVISION
																	CHK
																	APD

NO	COMPONENT NO	DESCRIPTION	QTY/M	U/M	
BILL OF MATERIAL					
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES					
UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.					
\odot	DENOTES CRITICAL CHARACTERISTICS.				
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE				
$\{ST\}$	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS				
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE				
COPIES TO	MATL SPEC SEE NOTES				
1 9 18	FINISH N/A				
2 10 19					
3 12 20					
4 13 21	DRW E/JIN	DATE 03/29/12	SCALE 1:1		
5 14 23	CHK	DATE	SUPER DR		
6 15 33	APPD	DATE	FINSH GOOD WT GRAMS/PIECE		
7 16 43					
8 17 53					
TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-FH)					
DIMENSION	0.5 - 3	3 - 6	6 - 30	30 - 120	120 - 400
TOLERANCE	± 0.05	± 0.05	± 0.1	± 0.15	± 0.2
3RD ANGLE PROJECTION	TITLE #10 CABLE SEAL				
	REVISION A	DRWG. NO. OL-868-952			
DES PLAINES, ILLINOIS 60016					

CAD GENERATED DRAWING - NO PENCIL CHANGES ALLOWED