

AFH SERIES ATO FUSE HOLDERS



Description

AFH Series ATO fuse holders are versatile holders for in-line or panel mount applications. Interlock body design allows fuse holders to be snapped together. Use with ATO® Fuse 1 to 20 amps (standard duty) or 25-30A (Heavy Duty). Supplied with 8" wire loop.

Web Resources

Download 2D print and technical resources at: littelfuse.com/AFHFuseHolders

Features and Benefits

- 8" looped wire leads for in-line installation
- Snap fit arms for panel mounting
- Interlocking body design allows multiple fuse holders to be snapped together
- UL94 V-2 Rated for Flammability Resistance

Specifications Overview

Max Voltage: 32V DC
Operating Temp: -40° C to +85° C

Recommended Fuses



ATO Fuse
 32V DC Fast Acting
 Automotive Blade Fuse

Ordering Information

PART NUMBER	DESCRIPTION	MAX FUSE RATING	WIRE SIZE	COLOR
0AFH0001XP	In-line Panel Mount ATO Fuse Holder - Carded Retail Packaging	20A	14 AWG	Black
0AFH0001Z	In-line Panel Mount ATO Fuse Holder - Bulk Packaging	20A	14 AWG	Black
0AFH0002XP	Heavy Duty In-line Panel Mount ATO Fuse Holder - Carded Retail Packaging	30A	10 AWG	Orange
0AFH0002Z	Heavy Duty In-line Panel Mount ATO Fuse Holder - Bulk Packaging	32A	10 AWG	Orange



Visit Littelfuse.com for the most up-to-date product information. Littelfuse products are designed for specific applications and should not be used for any purpose (including, without limitation, automotive applications) not expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse product documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse product documentation.