

# HPDM SERIES

## 70 V Max 600 A 2-Pole MEGA® Fuse Power Distribution Module



880195300



880195400

### Description

The HPDM Series 70 V Max 600 A 2-Pole MEGA® Fuse Power Distribution Module is a heavy-duty fuse box designed for OEM and aftermarket applications in heavy trucks, tractor-trailers, and agricultural and construction equipment.

When connected to a vehicle's electrical system, it provides two high-current MEGA® fuse-protected circuit outputs as well as an unfused output that can optionally be used to parallel multiple power distribution modules or deliver power to circuits that do not require circuit protection.

A separate fuse compartment provides a seal that protects the fuses and their terminations from harsh environments. This allows for permanent cable connections that can be dielectrically sprayed without affecting the fuses.

### Web Resources

Download 2D print, installation guide and technical resources at: [littelfuse.com/HPDM](http://littelfuse.com/HPDM)

### Ordering Information

PART NUMBER	DESCRIPTION	HOUSING	INPUT TERMINALS
880195300	70 V Max 600 A 2-Pole MEGA® Fuse Power Distribution Module with 250 A Fuses	Black Thermoplastic Base/ Black Polycarbonate Cover	3 x BOLT- M10 X 1.5 outside 1 x BOLT- M8 X 1.25 outside 4 x BOLT- M8 X 1.25 for 2 fuses
880195400	70 V Max 600 A 2-Pole MEGA® Fuse Power Distribution Module	Black Thermoplastic Base/ Black Polycarbonate Cover	3 x BOLT- M10 X 1.5 outside 1 x BOLT- M8 X 1.25 outside 4 x BOLT- M8 X 1.25 for 2 fuses

### Specifications

<b>Max Voltage Rating Continuous:</b>	48 V
<b>Max Voltage Rating</b>	70 V
<b>Max Total Continuous Current:</b>	600A
<b>Operating Temp Range:</b>	-50C to + 105°C
<b>Ingress Protection:</b>	IP67 & IP69K
<b>Mounting Method:</b>	M8 Bolt
<b>Mounting Hole:</b>	Ø8.50mm
<b>Fuse Type:</b>	MEGA®

### Applications

- Tractor-Trailers
- Heavy Trucks
- Agriculture
- Construction

### Features and Benefits

- Custom insert-molded studs for cable terminations and MEGA® fuse attachment result in high terminal torque capability and lower connection resistance
- Designed to minimize bridging corrosion between positive live metal surfaces and potentially grounded assembly hardware or mounting surfaces
- Metal inserts at the mounting holes allow for an increased assembly torque without distorting the base material
- Unfused terminal for optional daisy chaining multiple power distribution modules or providing power to circuits that cannot be fused
- AssureLatch™ Technology positive-sealing latches keep the MEGA® fuse holder cover securely in place while allowing for fast service
- Cover label recess allows optional addition of application-specific labels to the heavy-duty fuse box per end-customer requirement