

Model FLQ

File Number: E10480

COMPANY

LITTELFUSE INC
 8755 W Higgins Rd, Suite 500
 Chicago, IL 60631 United States

MODEL INFO

FLQ followed by 0.1 thru 30, may be followed by HXR.
 Supplemental fuses: time delay, paper tube, filled-tube, cartridge enclosed

SUPPLEMENTAL FUSES	VALUE
Micro Fuse	No
Pigtail Leads	No
Surface Mount	No
Cartridge Enclosed	Yes
Time Delay	Yes
Paper Tube	Yes
Filled Tube	Yes
OD - Length	10.32 mm
Length - Width	38.1 mm

RATING TABLE				
Amps Minimum (A)	Amps Maximum (A)	Voltage (V)	Voltage Source	Interrupting Rating (A)
0.1	0.2	500	ac	10000
0.25	7	500	ac	10000
8	9	500	ac	10000
10	12	500	ac	10000
14	15	500	ac	10000

RATING TABLE

Amps Minimum (A)	Amps Maximum (A)	Voltage (V)	Voltage Source	Interrupting Rating (A)
16	30	500	ac	10000

Report Date: 1990-06-25

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL Solutions' Follow - Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL Solutions' Follow - Up Service. Always look for the Mark on the product.

UL Solutions permits the reproduction of the material contained in Product iQ subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from Product iQ with permission from UL Solutions" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "©2024 UL LLC."