

PGB, PGA, PGG

REMOTE INDICATION		
Product	Features	Accessory For
<p>PGB-0302 Remote Indication and Reset Assembly</p> 	Panel-mounted remote indication and reset, standard 22 mm mounting with NEMA 4 and NEMA 13 rating.	PGR-5325
<p>PGB-0325 Remote Indication and Reset Assembly</p> 	Panel-mounted remote indication and reset with NEMA 1 rating.	PGR-5325
<p>PGA-0500 Analog % Current Meter</p> 	Panel-mounted analog am meter displays the Ground-Fault Current as a percentage of the set-point.	PGR-4300 PGR-5701 PGR-6100
<p>PGA-0510 Analog Ohm Meter</p> 	Panel-mounted analog ohmmeter displays the Insulation Resistance from 0 Ω to infinity.	PGR-3200 PGR-6100 PGR-8600

GROUND-REFERENCE MODULES		
Product	Features	Accessory For
<p>PGG-0024 Ground Reference Module</p> 	Connects the PGR-2601 relay to an ungrounded 24 Vdc bus.	PGR-2601
<p>PGG-0048 Ground Reference Module</p> 	Connects the PGR-2601 relay to an ungrounded 48 Vdc bus.	PGR-2601
<p>PGG-0125 Ground Reference Module</p> 	Connects the PGR-2601 relay to an ungrounded 125 Vdc bus.	PGR-2601
<p>PGG-0250 Ground Reference Module</p> 	Connects the PGR-2601 relay to an ungrounded 250 Vdc bus.	PGR-2601
<p>PGG-0500 Ground Reference Module</p> 	Connects the PGR-2601 relay to an ungrounded 500 Vdc bus.	PGR-2601
<p>PGG-0780 Ground Reference Module</p> 	Connects the PGR-2601 relay to an ungrounded 780 Vdc bus.	PGR-2601

Note: Contact factory for other voltages.