

RELAY SOCKETS



99025 Socket



99026 Socket

Description

Available as Form A (SPST) or Form C (changeover SPDT), with no suppressor / resistor suppressor / diode suppressor, sealed or unsealed.

Features and Benefits

- Sockets dovetail together.
- Accepts standard quick connect terminals.
- Accept Littelfuse Heavy Duty and High Power Relays & standard ISO relays.
- Bracket for easy mounting.
- Rugged glass-filled polyamide.
- Weatherproof construction.
- Temperature range -40 °C to 85 °C

Heavy Duty and High Power Relays



HEAVY DUTY RELAYS	
RELAY	VOLTAGE
NO 40A	12V DC
NC 30A	12V DC
NO 20A	24V DC
NC 15A	24V DC

HIGH POWER RELAYS	
RELAY	VOLTAGE
NO 70A	12V DC
NC 60A	12V DC
NO 35A	24V DC
NC 30A	24V DC

Applications

- 99025 - Use with Tyco (AMP) terminals 280756 or 280755
- 99026 - Use with Tyco (AMP) terminals 42281 or Ark-Les 3000H112A series

Web Resources

Download technical resources at:
littelfuse.com/RelaySockets

Ordering Information

PART NUMBER	DESCRIPTION
99025	Use with High Power Relays, Form A (SPST)
99026	Use with Heavy Duty Relays, Form A (SPST) or Form C (SPDT)

Datasheet Replaces Hotfeed Number D-600