


1-20A



35-60A


REVISION		
REV	DATE	DESCRIPTION
A	09/06/2013	509410GCP - RELEASE PER SALES RELEASE EM2461 MRY
B	10/28/2013	509611ECP/D - ADD 25-30A, CORRECT LENGTH MRY
C	11/21/2013	509817ECP/C - CHANGE FROM 6-15A TO 6-20A MRY
D	04/13/2015	514186ECP/D - ADD TOLERANCES, UPDATE 30A DESIGN, ADD DATA SHEET REV MRY
E	08/17/2015	514769ECP/D - UPDATE DATA SHEET REVS MRY
F	08/30/2016	516307ECP/D - UPDATE SPXV DATA SHEET REV MRY
G	6/6/17	517430ECP/D - REMOVE DATA SHEET REVISION, CHG 6-20A TO 4-20A MRY
H	9/5/17	518050ECP/C - CHG 4-20A TO 1-20A MRY
J	9/16/19	521247ECP/D - ADD 35-60A MRY
K	3/24/22	524962ECP/D - REMOVE 25-30A MRY

●	DENOTES CRITICAL CHARACTERISTICS.
CPK	DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE
⬡	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS.
CP	DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE.

B

MATL SPEC		FINISH	
DRW MYORK	DATE 1/18/2013	SCALE NTS	FINISH GOOD WT GRAMS/PIECE

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS, DIMENSIONS IN BRACKETS [] ARE INCHES DIMENSIONING AND DO NOT INCLUDE PLATING. TOLERANCING TO BE INTERPRETED IN ACCORDANCE WITH ANSI Y14.5M-1994



TITLE 1500VDC PHOTOVOLTAIC FUSE

 CHICAGO, ILLINOIS 60631	REVISION	DRWG NO.	SHEET 1 OF 1
	K	OL-SPXV000	