

# Model 438\*

File Number: E10480

## COMPANY

### LITTELFUSE INC

8755 W Higgins Rd, Suite 500  
Chicago, IL 60631 United States

## MODEL INFO

438\*

Supplemental micro fuses: surface mount

SUPPLEMENTAL FUSES	VALUE
Micro Fuse	Yes
Pigtail Leads	No
Surface Mount	Yes
Cartridge Enclosed	No
Time Delay	No
Paper Tube	No
Filled Tube	No
OD - Length	1.54 mm
Length - Width	0.85 mm
Height	0.5 mm

RATING TABLE				
Amps Minimum (A)	Amps Maximum (A)	Voltage (V)	Voltage Source	Interrupting Rating (A)
0.25	1.75	63	dc	50

**RATING TABLE**

<b>Amps Minimum (A)</b>	<b>Amps Maximum (A)</b>	<b>Voltage (V)</b>	<b>Voltage Source</b>	<b>Interrupting Rating (A)</b>
0.25	1.75	63	dc	50
0.25	1.75	32	ac	50
0.25	1.75	32	ac	50
2	5	32	dc	50
2	5	32	dc	50
6	6	24	dc	50
6	6	24	dc	50
2	6	12	ac	50
2	6	12	ac	50

Report Date: 2008-08-12

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL Solutions' Follow - Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL Solutions' Follow - Up Service. Always look for the Mark on the product.

UL Solutions permits the reproduction of the material contained in Product iQ subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from Product iQ with permission from UL Solutions" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "©2024 UL LLC."