


- NOTES:
1. MAX. RATING 30A, 32 VOLTS AT A MAXIMUM OPERATING TEMPERATURE OF 82° C.
 2. BODY MATERIAL: ALCRYN, BLACK
COVER MATERIAL: ALCRYN, BLACK
 3. WIRE: 12 GA, COLOR: ORANGE

CUSTOMER: FORD
CUSTOMER P/N: YW1T-14517-AA

NO		COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL					
COPIES TO		MATL SPEC		FINISH	
1	9	18	DRW	BJJ	DATE 5/26/99
2	10	19	CHK		SCALE 1:1
3	12	20	CHK		DATE SUPER DRW
4	13	21	APPD		DATE RAW STK WT
5	14	23			LBS/M
6	15	33			TOLERANCE UNLESS OTHERWISE SPECIFIED
7	16	43			TWO PLACE DEC ±.01
8	17	53			THREE PLACE DEC ±.005
TITLE					
MINIFUSE HOLDER, IN LINE					
LTR		REVISION		CHK	APD
A	07944	5/26/99	RELEASED	BJJ	
B	39954B	06/22/99	MODIFY DIMS., ADD CUSTOMER INFO	PJM	


Littelfuse
 DES PLAINES, ILLINOIS 60016
 DRAWING NO. 01530023Z
 OUTLINE

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.

DENOTES CRITICAL CHARACTERISTICS.

DENOTES CPK DIMENSIONS.-MINIMUM CPK VALUE ----

DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. REFERENCE PROCEDURE FOR MEASUREMENT OF THIS CHARACTERISTIC IN THE INSTRUCTIONS.

DENOTES CP DIMENSIONS.-MINIMUM CP VALUE

DENOTES DIMENSIONS WITHIN THE DIMENSIONAL LIMITATIONS AND TOLERANCES SPECIFIED IN THE DIMENSIONALLY LOCATED TOOLS FOR MAXIMUM TOOL LIFE.

CONTROLLED DOCUMENT