


- NOTES:
1. MAX. RATING (SEE CHART), 32 VOLTS AT A MAXIMUM OPERATING TEMPERATURE OF 82° C.
 2. BODY MATERIAL: ALCRYN, BLACK
COVER MATERIAL: ALCRYN, BLACK
 3. COVER TETHER IS SLID ON EITHER WIRE LEAD AND SEATED IN BODY GROOVE.
 4. FUSEHOLDER IS SHIPPED WITH COVER ATTACHED BUT NOT SNAPPED ON THE BODY.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.

DENOTES CRITICAL CHARACTERISTICS.
 DENOTES CPK DIMENSIONS.-MINIMUM CPK VALUE
 DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE AND PROCEDURE FOR MEASUREMENT (STANDARD TEST METHOD).
 DENOTES CP DIMENSIONS.-MINIMUM CP VALUE
 DIMENSIONS WITHIN THE DIMENSIONAL LIMITATIONS ABOVE ARE UNLESS OTHERWISE SPECIFIED, DIMENSIONALLY LOCATED TO A MAXIMUM TOOL LIFE.

UNCONTROLLED DOCUMENT

NO		COMPONENT NO	DESCRIPTION	QTY/M	U/M
BILL OF MATERIAL					
COPIES TO		MATL SPEC		FINISH	
1	9	18	DRW	PJM	DATE 9/4/01
2	10	19	CHK	DATE	SCALE 1:1
3	12	20	APPD	DATE	SUPER DRW
4	13	21	DATE	DATE	RAW STK WT
5	14	23	DATE	DATE	LBS/M
6	15	33	DATE	DATE	
7	16	43	DATE	DATE	TOLERANCE UNLESS OTHERWISE SPECIFIED
8	17	53	DATE	DATE	TWO PLACE DEC ±.01
					THREE PLACE DEC ±.005
					ANGULAR ±1°
TITLE					
MINIFUSE HOLDER, IN LINE					
LTR		REVISION		CHK	APD
A	60655	RELEASE 9/4/01 PJM			


 DES PLAINES, ILLINOIS 60016

DRAWING NO. SERIES OUTLINE
 A 01530028Z