



- NOTES:
1. MAX. RATING, 20 AMPS, 32 VOLTS AT A MAXIMUM OPERATING TEMPERATURE OF 82° C.
 2. BODY MATERIAL: ALCRYN, BLACK
COVER MATERIAL: ALCRYN, BLACK
 3. COVER TETHER IS SLID ON EITHER WIRE LEAD AND SEATED IN BODY GROOVE.
 4. FUSEHOLDER IS SHIPPED WITH COVER ATTACHED BUT NOT SNAPPED ON THE BODY.

| NO | | COMPONENT NO | DESCRIPTION | QTY/M | U/M |
|--------------------------|-------|--------------|-------------|--------------|--------------------------------------|
| BILL OF MATERIAL | | | | | |
| COPIES TO | | MATL SPEC | | FINISH | |
| 1 | 9 | 18 | DRW | PJM | DATE 10/15/01 |
| 2 | 10 | 19 | CHK | DATE | SCALE 1:1 |
| 3 | 12 | 20 | APPD | DATE | SUPER DRW |
| 4 | 13 | 21 | DATE | DATE | RAW STK WT |
| 5 | 14 | 23 | DATE | DATE | LBS/M |
| 6 | 15 | 33 | DATE | DATE | TOLERANCE UNLESS OTHERWISE SPECIFIED |
| 7 | 16 | 43 | DATE | DATE | TWO PLACE DEC ±.01 |
| 8 | 17 | 53 | DATE | DATE | THREE PLACE DEC ±.005 |
| TITLE | | | | | |
| MINIFUSE HOLDER, IN LINE | | | | | |
| LTR | | REVISION | | CHK APD | |
| A | 60683 | RELEASE | | 10/15/01 PJM | |

UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.

DENOTES CRITICAL CHARACTERISTICS.

DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE

DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE AND PROCEDURE FOR MEASUREMENT OF THIS CHARACTERISTIC. SEE INSTRUCTIONS FOR MEASUREMENT OF THIS CHARACTERISTIC.

DENOTES CP DIMENSIONS, -MINIMUM CP VALUE

DENOTES DIMENSIONS WITHIN THE DIMENSIONAL LIMITATIONS AND TOLERANCES SPECIFIED IN THE DIMENSIONALLY LOCATED TOOLS AND EQUIPMENT LIST FOR MAXIMUM TOOL LIFE.

DES PLAINES, ILLINOIS 60016
 DRAWING NO. SERIES OUTLINE
 A 01530029Z

UNCONTROLLED DOCUMENT