



NOTE:

ALL DIMENSIONS ARE IN MILLIMETERS,
ENGLISH DIMENSIONS ARE IN [].

CERTIFICATION OF
COUNTRY OF ORIGIN
REQUIRED

| | | | | | | | | | |
|--|---|-----------|--------------------|---------------|-------|--------------|------------|---|-------|
| COPIES TO | MAT'L. SPEC. | | FINISH | | SCALE | | SUPER. DR. | LBS./M | |
| | 18 | 19 | Nylon Color: Black | | 1 | | | | |
| 9 | 10 | 12 | 13 | 14 | 15 | 16 | 17 | 18 | |
| 1 | 2 | 3 | 4 | 5 | 6 | 7 | 8 | 9 | |
| DR. Ges. Apr. 7 94 | | CHK. Ges. | | DATE 10-11-94 | | RAW STK. WT. | | TOLERANCE UNLESS OTHERWISE SPECIFIED | |
| APPD. | | | | | | | | TWO PLACE DEC. ± 0.50mm [0.020] | |
| | | | | | | | | THREE PLACE DEC. ± 0.25mm [0.010] ANGULAR ± | |
| TITLE 4 POSITION MAXI FUSE MODULE | | | | | | | | | |
| Littelfuse® 800 E. NORTHWEST HIGHWAY DES PLAINES, ILLINOIS 60016 | | | | | | | | | |
| DRWG. NO. E-03540505Z | | | | | | | | | |
| LTR | REVISION | | | | | | | CHK. | APPD. |
| A | 06534 - RELEASED October 10, 94 Ges. | | | | | | | Ges | AF |
| B | 36644D - CHG - 2 PLACE TOLERANCE .010 TO .020 CHG 2 PLACE TOLERANCE .020 TO .010 2-10-95 | | | | | | | Ges | Ges |
| C | 36988 L - ADD METRIC DIM'S 7-19-95 RFR | | | | | | | Ges | Ges |
| D | 37055D - CHG TITLE 8-19-95 JCU | | | | | | | TJR | Ges |
| E | 000807E - 10-9-09 REINSTATE JCU | | | | | | | | |

DRAWING NO.