

Military Midget 10x38 mm Fuses

592 Series

Commercial Equivalent = [KLK Series](#)



Description

With a vast network of manufacturing and engineering facilities and a global system of distribution channels, Littelfuse offers a variety of switchgear fuses to meet your specific needs, including military high-reliability fuses.

Features & Benefits

FEATURES	BENEFITS
10x38 mm size	Common dimensions used in a variety of applications
Fast-acting	Provides fast, reliable short-circuit response within the interrupting rating
POWR-GARD® technology	Ensures quality overcurrent protection

Applications

- Control circuits
- Street and HID lighting
- Computers

Approved to MIL-PRF-15160/60

MIL TYPE DESIGNATION	NICKEL-PLATED CAPS	MIL TYPE DESIGNATION	NICKEL-PLATED CAPS
60C 500V ¼A	592.125	F60C 500V 3A	592.003
F60C 500V ⅜A	592.200	F60C 500V 4A	592.004
F60C 500V ¼A	592.250	F60C 500V 5A	592.005
F60C 500V ⅜A	592.300	F60C 500V 6A	592.006
F60C 500V ¾A	592.375	F60C 500V 8A	592.008
F60C 500V ½A	592.500	F60C 500V 10A	592.010
F60C 500V ¾A	592.750	F60C 500V 15A	592.015
F60C 500V 1A	592.001	F60C 500V 20A	592.020
F60C 500V 1½A	592.015	F60C 500V 25A	592.025
F60C 500V 2A	592.002	F60C 500V 30A	592.030

Note: Boldface numbers indicate series; light type numbers indicate amperage value.

Disclaimer Notice – Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at www.littelfuse.com/product-disclaimer.