



7496

MM	IN
15	010
52	060
48	334
55	337
11 93	470
12 96	510
22 35	880
33 52	1,320
63 00	2,520



8.0 OHMS ± 10%

DO NOT SCALE

LET	WAS	DATE	BY	LET	WAS	DATE	BY	MATERIAL	DRAWN	CHECKED	APPRV D	SCALE	DATE DRAWN
								NOTED	R6	FY		11	3-2-59
								FINISH NOTED					DATE BLUEPRINT
								TOLERANCES					
				F	REDRAWN	3-6-80	(R)	DECIMAL ± .010 METRIC ± .25	RHEOSTAT SWITCH				7496

CH 188(4 78)