


9238-01

MM	IN
5.84	.23
22.09	.87
22.60	.89
26.67	1.05
28.44	1.12
28.95	1.14



NOTE:
 ⓑ 1. ALL STL. PARTS PLATED
 Ⓒ 2. CAP. & NUT ASSY & ONE HEX NUT SHIPPED LOOSE & ONE HEX NUT ASSEMBLED

20 AMPS - 12 VOLTS

DO NOT SCALE

LET	WAS	DATE	BY	LET	WAS	DATE	BY	MATERIAL	DRAWN	CHECKED	APPRV D	SCALE	BASIC EXCEPT W/ CAP & NUT ASSY	DATE DRAWN
								#	EA	S.J.B. 6-1-88		1=1		7-31-73
								FINISH	 20 OLD COLONY AVENUE SOUTH BOSTON, MA U.S.A. 02127					DATE BLUEPRINT
				C	ECN 265-H HEX NUT ASSEMBLED	3/19/97	JMP	#						
				B	CAD OR ZINC 25234	11/9/92	JH	TOLERANCES	MOMENTARY SWITCH					9238-01
				A	REDRAWN	5/31/88	-JK	DECIMAL ± METRIC ±						

CH-188(4-78)