



ATO<sup>®</sup> Shunt

ATO<sup>®</sup> Shunt

Specifications

|                                   |                                              |
|-----------------------------------|----------------------------------------------|
| *Recommended Environmental Temp.: | -40°C to +125°C                              |
| Max. Continuous Load Rating:      | 35A * *                                      |
| Housing Material:                 | Thermoplastic (UL 94 Flammability Rating V0) |
| Terminal Material:                | Tin Plated Brass                             |



\*Tin plating's temperature limit is ≈130°C  
\*\*Rating varies based on mating terminal performance

Ratings

| Part Number | Max Continuous Load Rating** (A) | Housing Material        | Terminal Material | Part Quantity |
|-------------|----------------------------------|-------------------------|-------------------|---------------|
| 02400094P   | 35                               | Thermoplastic (UL 94V0) | Tin Plated Brass  | 2000          |