

00200400 & 00201000 CONNECTORS

ADR Cables • Polyurethane sheath material



00200400
00200600
00201000



00200500
00201100

Description

ADR cable resists UV-ray and low temperatures, as well as being resistant to oil, weathering and chemicals thanks to the PUR sheathing. In addition they provide for higher resistance against wear, abrasion, microbiotic attack and hydrolysis. The cables have been produced in accordance with the latest international standards ISO 4141 and ISO 6722.

Features and Benefits

- Standards: Conforms to ISO 4141 & ISO 6722 recommendations and standards.
- Wire insulation and inner sheath: PVC
- Sheath: PUR
- Min/Max temperatures: -40°C / +85°C.

Specifications Overview

Voltage: 12V/24V
Standards: ISO 4041
ISO 6722

Web Resources

Download technical resources at:
littelfuse.com/connectors

Ordering Information

PART NUMBER	MATERIAL	NUMBER AND SECTION OF WIRES	EXTERNAL DIAMETER	ROLL	APPLICATION
00200400	Polyurethane	2x1 mm ²	6,5 mm	50 m	SIDE-MARKER
00200500	Polyurethane	2x1 mm ²	6,5 mm	500 m	SIDE-MARKER
00200600	Polyurethane	5x1 mm ²	8,5 mm	50 m	-
00201000	Polyurethane	9x1 mm ² + 1x2 mm ²	11,1 mm	50 m	-