

ST ATO® SERIES FUSE BLOCK WITH GROUND BUS



880027



880028

Description

ST ATO® Fuse Blocks provide a cost effective, consolidated circuit protection solution. Designed to accept standard ATO® fuses, these products ensure the safe distribution of power throughout an application. These products are RoHS compliant. Fuses sold separately.

Features

- Snap-on insulating cover (included) with label recesses & spare fuse holder
- Screw termination
- Integrated negative busbar
- Includes sheet of circuit identification labels

Ordering Information

PART NUMBER	DESCRIPTION	PACKAGING
880027	6 ATO® ST Fuse Block w/ Ground	Bulk
880027-BP	6 ATO® ST Fuse Block w/ Ground Blister Pack	Blister Pack
880028	12 ATO® ST Fuse Block w/ Ground	Bulk
880028-BP	12 ATO® ST Fuse Block w/ Ground Blister Pack	Blister Pack

Specifications

Current Rating Max:	100A
Current Rating Max Per Circuit:	30A Max
Fuse Type:	ATO® Blade Fuse
Housing:	PBT
Input Terminals:	10-32 Stud
Mounting Method:	Bolt-Down; 4xM5
Number Of Cavities:	6 or 12 Circuits (varies by part number)
Output Terminals:	10-32 Screw
Recommended Torque:	8 in-lb (0.9Nm) Max.
Temperature:	-20°C to 85°C
Max Voltage Rating:	32V DC

Applications

- Centralized distribution for accessory circuits
- Ideal solution for DIY projects

Benefits

- Centralizes wiring to a convenient location
- Insulating cover provides circuitry protection
- Continuous current rating of 100A

Related Products



SD ATO® Fuse Blocks

Designed to accept ATO® fuses.



SD MINI® Fuse Blocks

Designed to accept MINI® fuses.

Web Resources

Download 2D print, installation guide and technical resources at: littelfuse.com/ST-ATO

ST ATO® SERIES FUSE BLOCK WITH GROUND BUS

Circuit Identification Labels

