

# MAXI® MAH SERIES IN-LINE BLADE FUSE HOLDER



MAHC0001TXJ

MAHC0001ZXJ

## Description

The MAXI® MAH Series 32V In-Line Blade Fuse Holder with 6 Gauge Leads is an easy-to-install bulkhead fuse holder that's ideal for protecting air conditioner, high-amp audio, heater blower motor, and air compressor circuits.

The tethered fuse holder cover protects an installed MAXI® blade-style fuse up to 60 amps (sold separately) against harsh underhood conditions, while the center hole in the housing makes it simple to mount the fuse holder to a bulkhead.

The MAXI® MAH Series in-line fuse holder comes with either 5" (127mm) or 5.9" (150mm) leads.

## Web Resources

Download 2D print, installation guide and technical resources at: [littelfuse.com/MAH](http://littelfuse.com/MAH)

## Ordering Information

PART NUMBER	DESCRIPTION	CURRENT RATING MAX	FUSE TYPE	MOUNTING METHOD	MAX VOLTAGE RATING
MAHC0001TXJ	32V In-Line Blade Fuse Holder with 6 Gauge Leads - 5" Black Leads - 10 Pcs.	60 Amps	MAXI	In-Line Fuse Holder	32V
MAHC0001ZXJA	32V In-Line Blade Fuse Holder with 6 Gauge Leads - 5" Red Leads	60 Amps	MAXI	In-Line Fuse Holder	32V
MAHC0001ZXJB	32V In-Line Blade Fuse Holder with 6 Gauge Leads - 5.9" Black Leads	60 Amps	MAXI	In-Line Fuse Holder	32V
MAHC0001ZXJ	32V In-Line Blade Fuse Holder with 6 Gauge Leads - 5" Black Leads - 100 Pcs.	60 Amps	MAXI	In-Line Fuse Holder	32V
MAHC-BP	32V In-Line Blade Fuse Holder with 6 Gauge Leads - 5" Black Leads - Blister Pack - 100 Pcs.	60 Amps	MAXI	In-Line Fuse Holder	32V

## Specifications

<b>Current Rating Continuous:</b>	45 Amps
<b>Current Rating Max:</b>	60 Amps
<b>Current Rating Max Terminal:</b>	60 Amps
<b>Fuse Type:</b>	MAXI
<b>Ignition Protection:</b>	V-2
<b>Ignition-Proof:</b>	UL- 94
<b>Input Terminals:</b>	MAXI Fuse Blades
<b>Mounting Method:</b>	In-Line Fuse Holder
<b>Temperature in Celsius:</b>	Max. Operating Temperature of 80°C
<b>Max Voltage Rating:</b>	32VDC
<b>Wire Description:</b>	150°C rated, UL-3288 Black wires
<b>Wire Size:</b>	6 AWG

## Features and Benefits

- Compatible with MAXI® blade-style fuses up to 60 amps (sold separately)
- 6 gauge UL3288-rated wire leads for an easy-to-install in-line fuse holder design
- Heat-resistant thermoplastic housing is ideal for automotive applications
- Center body hole enables easy mounting to a bulkhead
- Tethered cover protects against splashes and debris
- UL 94 V-2 flammability rating

## Applications

- Air Conditioners
- High-Amp Audio Equipment
- Heater Blower Motor
- Air Compressors