

MEGA® 298 SPLASHPROOF SERIES FUSE HOLDER



Assembled Product, Fuse Not Included

Description

The Littelfuse 70V Bolt-Down MEGA® 298 Splashproof Series Fuse Holder is designed to mount and encase any MEGA® bolt-down fuse with a current rating up to 250A. When mated, the nylon MEGA® 298 Splashproof base (298907-030) and cover (298907-040), each sold separately, provide splashproof protection using a silicone O-ring and grommets. This MEGA® bolt-down fuse holder is ideal for battery and alternator connections as well as other types of heavy gauge cables that require ultra-high current protection.

Features and Benefits

- Compatible with MEGA® fuses with a current rating of up to 250A (fuse not included)
- Silicone O-ring and grommets create a splashproof seal when the fuse holder is fully assembled (base and cover sold separately)
- Interconnecting pins on the side of the fuse holder allow for multiple block configurations
- M8 stud input and output terminals

Ordering Information

PART NUMBER	DESCRIPTION	CURRENT RATING MAX	FUSE TYPE	MOUNTING METHOD	MAX VOLTAGE RATING	IGNITION PROTECTION
298907-030	70V Bolt-Down MEGA® 298 Splashproof Series Fuse Holder Base	250A	MEGA (298)	Plastic tab with M6 hole	70V	B/16.3
298907-040	70V Bolt-Down MEGA® 298 Splashproof Series Fuse Holder Cover	-	-	Plastic tab with M3.8 hole (Mates with 298907-030 base)	-	DNI

Specifications

Current Rating Continuous:	250A
Current Rating Max:	250A
Current Rating Max Terminal:	250A
Fuse Type:	MEGA (298)
Ignition Protection:	Base: B/16.3 Cover: DNI
Ignition-Proof:	ISO 3795
Input Terminals:	M8 Stud
Mounting Method:	Plastic tab with M6 hole Plastic tab with M3.8 hole (Mates with 298907-030 base)
Output Terminals:	M8 Stud
Recommended Torque:	M8 Jam Nut: 5.65 Nm (15 In-Lbs) Min.
Max Voltage Rating:	70V

Applications

- Battery and Alternator Connections

Web Resources

Download 2D print, installation guide and technical resources at: littelfuse.com/298-splashproof