



RESISTANCE @ +25°C = 3,000 Ω ± 10%
 RESISTANCE/TEMPERATURE CURVE = "J"
 BETA "β" (+25 TO +85°C) = 3,977°K NOMINAL
 TEMPERATURE COEFFICIENT @ +25°C = -4.4%/°C NOMINAL
 DISSIPATION CONSTANT = 1.3 mW/°C NOMINAL (AIR)
 THERMAL TIME CONSTANT = 14 SECONDS NOMINAL (AIR)
 MAXIMUM TEMPERATURE RATING = +300°C

SEE MANUFACTURING SPECIFICATION (LAYER 1)

NONE	RELEASE TO PRODUCTION	02/20/14	DD
REV	REVISION RECORD	DATE	APP

SCALE NONE	U.S. SENSOR CORP. © COPYRIGHT 714-639-1000 www.ussensor.com NTC THERMISTOR P/N GR302J1K
DRAWN BY DAN DANKERT	
DATE 02/20/14	
REV. NONE	
LAYER 0 OF 2	