



RESISTANCE @ +77°F (+25°C) = 100,000 Ω NOMINAL  
 ACCURACY (+55 TO +85°F) (+12.8 TO +29.4°C) = ± 0.50°F (± 0.28°C)  
 RESISTANCE TEMPERATURE CURVE = "J"  
 TEMPERATURE COEFFICIENT @ +77°F (+25°C) = -4.4%/°C NOMINAL  
 BETA "β" (+32 TO +122°F) (0 TO +50°C) = 3,892°K NOMINAL  
 DISSIPATION CONSTANT = 2 mW/°C NOMINAL (STILL AIR)  
 MAXIMUM TEMPERATURE RATING = +572°F (+300°C)

\*\*\* ROHS COMPLIANT \*\*\*

SUPPLIED ON TAPE & REEL PER EIA-296-E

"A"	ADDED TAPE & REEL REQUIREMENT	07/15/10	DD
NONE	RELEASE TO PRODUCTION	03/09/10	DD
REV	REVISION RECORD	DATE	APP

SCALE	NONE	© COPYRIGHT <b>U.S. SENSOR CORP.</b> 714-639-1000 www.ussensor.com <b>NTC THERMISTOR</b> P/N 104JM2B
DRAWN BY	DAN DANKERT	
DATE	03/09/10	
REV	"A"	
LAYER	0 OF 1	