



RESISTANCE @ +25°C = 1,000,000 Ω ± 10%  
 RESISTANCE/TEMPERATURE CURVE = "V3"  
 TEMPERATURE COEFFICIENT @ +25°C = -4.93%/°C NOMINAL  
 BETA "β" (0 TO +50°C) = 4,369°K NOMINAL  
 DISSIPATION CONSTANT = 2 mW/°C NOMINAL (STILL AIR)  
 THERMAL TIME CONSTANT = 5 SECONDS NOMINAL (STILL AIR)  
 THERMAL TIME CONSTANT = 0.5 SECONDS NOMINAL (STIRRED OIL)  
 MAXIMUM TEMPERATURE RATING = +300°C

---	ISO RELEASE	09/21/04	DD
"A"	LEAD WIRE DIAMETER WAS 0.020" ± 0.001"	09/21/04	DD
REV	REVISION RECORD	DATE	APP

SCALE	NONE	© COPYRIGHT <b>U.S. SENSOR CORP.</b> 714-639-1000 www.ussensor.com <b>NTC THERMISTOR</b> P/N 105V3G1K
DRAWN BY	DAN DANKERT	
DATE	09/26/95	
REV.	"A"	
LAYER	0 OF 1	