


0.020" ± 0.002" DIAMETER,  
24 AWG, TINNED CCS,  
1.0" LONG MINIMUM



RESISTANCE @ +25°C = 20,000 Ω ± 5%  
RESISTANCE/TEMPERATURE CURVE = "J"  
BETA "β" (0 TO +50°C) = 3,892°K NOMINAL  
TEMPERATURE COEFFICIENT @ +25°C = -4.4%/°C NOMINAL  
DISSIPATION CONSTANT = 2 mW/°C NOMINAL (STILL AIR)  
THERMAL TIME CONSTANT = 5 SECONDS NOMINAL (STILL AIR)  
THERMAL TIME CONSTANT = 0.5 SECONDS NOMINAL (STIRRED OIL)  
MAXIMUM TEMPERATURE RATING = +300°C

---	ISO RELEASE	12/10/03	DD
"A"	LEAD WIRE DIAMETER WAS 0.020" ± 0.001"	12/10/03	DD
REV	REVISION RECORD	DATE	APP

SCALE NONE	<b>U.S. SENSOR CORP.</b> 1832 W. COLLINS AVE. ORANGE, CA. 92867 714-639-1000 www.ussensor.com
DRAWN BY T. SOMERVILLE	
DATE 03/27/90	
REV. "A"	
LAYER 0 OF 1	
<b>NTC THERMISTOR</b>	
<b>P/N 203JG1J</b>	