



RESISTANCE @ +25°C = 0.7 Ω ± 25%
 MAXIMUM STEADY STATE CURRENT = 13 AMPS
 RESISTANCE @ MAXIMUM CURRENT = 0.025 Ω NOMINAL

DIM "D" = 1.175" MAXIMUM
 DIM "T" = 0.350" MAXIMUM
 DIM "L" = 0.700" MINIMUM
 DIM "S" = 0.310" OR 0.390" NOMINAL

LEAD WIRE GAUGE = 0.040" NOMINAL DIAMETER

SEE MANUFACTURING SPECIFICATION (LAYER 1)

NONE	RELEASE TO PRODUCTION	12/02/10	DD
REV	REVISION RECORD	DATE	APP

SCALE	NONE	© COPYRIGHT U.S. SENSOR CORP. 714-639-1000 www.ussensor.com INRUSH CURRENT LIMITER P/N STOR713B
DRAWN BY	DAN DANKERT	
DATE	12/02/10	
REV.	NONE	
LAYER	0 OF 2	