

Specification Status: Released

Operating Conditions at 20°C:


Maximum Continuous Operating Voltage (V_{MCO}): 60V_{DC}
Maximum Interrupt Current (I_{INT}): 3A_{RMS}

Fault Ratings at 20°C:

250V_{RMS}, 3A, 10 applications

Additional Info at 20°C:

- Resistance matched: N/A
- Lightning withstand:
 - ITU-T K.20, K21 - 1.5 kV
 - ITU-T K.20, K21 - 4.0 kV when tested with 230V GDT primary protector
- Helps equipment meet ITU-T K.20, K.21 Recommendations
- Helps equipment meet Telcordia GR1089 intrabuilding requirements



Marking:




TABLE I. DIMENSIONS:

	A		B		C	
	MIN	MAX	MIN	MAX	MIN	MAX
mm:	6.9	7.1	6.9	7.1	1.3	1.6
in.*	(0.27)	(0.28)	(0.27)	(0.28)	(0.05)	(0.06)

*Rounded off approximation.

TABLE II. PERFORMANCE RATINGS @ 20°C (as measured in test board # T2978):

HOLD* CURRENT (A)	TRIP* CURRENT (A)	RESISTANCE (Ω)			TIME TO TRIP(Sec) @ 1A*		OPERATING TEMPERATURE (°C)		TRIPPED POWER DISSIPATION (W) @ 60V _{DC} *	
		R MIN	R MAX	R ₂₄ MAX**	TYP	MAX*	MIN	MAX	TYP	MAX
0.180	0.38	1.9	3.0	4.2	3.4	6.5	-40	85	0.8	0.9

* Dependent on Heat Sinking of Mounting Fixture.

**Maximum device resistance at 20°C measured 24 hour post trip

TABLE III. APPLICABLE PART DESCRIPTIONS:

PART DESCRIPTION	PACKAGING TYPE	NOTES
TCF250-180T	Bulk	N/A

Agency Recognitions: UL (File # E74889)
Reference Documents: PS300, ITU-T K.20, K.21
Precedence: This specification takes precedence over documents referenced herein.
Effectivity: Reference documents shall be the issue in effect on the date of invitation for bid.
CAUTION: Operation beyond the rated voltage or current may result in rupture, electrical arcing or flame.

Materials Information

ROHS Compliant

Directive 2002/95/EC
Compliant

ELV Compliant

Directive 2000/53/EC
Compliant

Pb-Free



Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, military, aerospace, medical, lifesaving, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse.