



RTD ELEMENT RESISTANCE @ 0°C = 1,000 Ω ± 0.06%

RTD ELEMENT ACCURACY @ 0°C = ± 0.30°C

TCR = 3,850ppm/°C

DIN43760 ACCURACY CLASS = "B"

TEMPERATURE RATING = -50 TO +105°C

MOUNTING HOLE DIAMETER = 0.171" ± 0.008"

MOUNTING HOLE STUD SIZE = #8

SEE MANUFACTURING SPECIFICATION (LAYER 1)

NONE	RELEASE TO PRODUCTION	08/31/06	DD
REV	REVISION RECORD	DATE	APP

SCALE NONE	U.S. SENSOR CORP. 1832 W. COLL INS AVE. ORANGE, CA. 92867 714-639-1000 www.ussensor.com
DRAWN BY DAN DANKERT	
DATE 08/31/06	RTD PROBE
REV. NONE	P/N USW2299
LAYER 0 OF 2	