



PART NUMBER	PACKAGING
KR272G0J-1	BULK
KR272G0J-2	TAPE & REEL

RESISTANCE @ +25°C = 2,700 Ω ± 5%  
 RESISTANCE/TEMPERATURE CURVE = SEE KR272G0J R-T TABLE  
 BETA "β" (+25 TO +85°C) = 3,750°K NOMINAL  
 POWER RATING = 240 mW  
 TEMPERATURE RATING = -40 TO +125°C

PACKAGING: SEE TABLE

ROHS COMPLIANT

SEE MANUFACTURING SPECIFICATION (LAYER 1)

NONE	RELEASE TO PRODUCTION	04/27/17	DD
REV	REVISION RECORD	DATE	APP

SCALE	NONE	U.S. SENSOR CORP. © COPYRIGHT 714-639-1000 www.ussensor.com NTC CHIP THERMISTOR P/N KR272G0J-
DRAWN BY	DAN DANKERT	
DATE	04/27/17	
REV.	NONE	
LAYER	0 OF 2	