

RESISTANCE/TEMPERATURE TABLE


TEMP (°C)	RESIS (Ω NOM)	TEMP (°C)	RESIS (Ω NOM)
-40	16,161,000	45	216,220
-35	11,765,000	50	177,690
-30	8,634,400	55	146,780
-25	6,392,200	60	121,850
-20	4,774,800	65	101,630
-15	3,599,400	70	85,158
-10	2,738,100	75	71,662
-5	2,101,200	80	60,553
0	1,625,800	85	51,365
5	1,267,500	90	43,732
10	995,100	95	37,364
15	786,350	100	32,032
20	625,200	105	27,550
25	500,000	110	23,772
30	402,140	115	20,577
35	325,230	120	17,868
40	264,470	125	15,566

RESISTANCE @ +25°C = 500,000 Ω ± 5%  
 BETA "β" (+25 TO +85°C) = 4050°K NOMINAL  
 POWER RATING = 320 mW  
 OPERATING TEMPERATURE RANGE = -40 TO +125°C

PACKAGING: SEE TABLE

SEE MANUFACTURING SPECIFICATION (LAYER 1)

PART NUMBER	PACKAGING
LR504MOJ-1	BULK
LR504MOJ-2	TAPE & REEL



NONE	RELEASE TO PRODUCTION	11/10/17	MW
REV	REVISION RECORD	DATE	APP

SCALE NONE	U.S. SENSOR CORP. © COPYRIGHT 714-639-1000 www.ussensor.com
DRAWN BY MARCUS WEAST	
DATE 11/10/17	NTC THERMISTOR
REV. NONE	P/N LR504MOJ
LAYER 0 OF 2	