



RESISTANCE @ +25°C = 3,000 Ω ± 10%  
 RESISTANCE/TEMPERATURE CURVE = "F"  
 BETA "β" (0 TO +50°C) = 3,419°K NOMINAL  
 TEMPERATURE COEFFICIENT @ +25°C = -3.86%/°C NOMINAL  
 DISSIPATION CONSTANT = 1 mW/°C NOMINAL  
 THERMAL TIME CONSTANT = 5 SECONDS MAXIMUM  
 MAXIMUM TEMPERATURE RATING = +220°C

---	ISO RELEASE	02/23/05	DD
REV	REVISION RECORD	DATE	APP

SCALE NONE	U.S. SENSOR CORP. © COPYRIGHT 714-639-1000 www.ussensor.com
DRAWN BY DAN DANKERT	
DATE 06/10/02	NTC THERMISTOR
REV NONE	P/N MM302F1K
LAYER 0 OF 1	