



RESISTANCE @ +25°C = 3,000 Ω ± 10%  
 RESISTANCE/TEMPERATURE CURVE = "J"  
 BETA "β" (0 TO +50°C) = 3,892°K NOMINAL  
 TEMPERATURE COEFFICIENT @ +25°C = -4.4%/°C NOMINAL  
 DISSIPATION CONSTANT = 3 mW/°C NOMINAL  
 THERMAL TIME CONSTANT = 8 SECONDS MAXIMUM  
 MAXIMUM TEMPERATURE RATING = +220°C

---	ISO RELEASE	06/12/07	DD
REV	REVISION RECORD	DATE	APP

SCALE NONE	© COPYRIGHT <b>U.S. SENSOR CORP.</b> www.ussensor.com sales@ussensor.com <b>NTC THERMISTOR</b> <b>P/N SB302J1K</b>
DRAWN BY DAN DANKERT	
DATE 10/08/02	
REV. NONE	
LAYER 0 OF 1	