


STANDARD HEAVY DUTY TOGGLE SWITCHES



55014



55021



5582



5588



55065-02



55021-07

Description

Littelfuse Toggle Switches are designed for universal applications within harsh environments. Their mounting, body, and actuator features are designed for ease-of-use and extended product lifecycle.

The Standard Heavy Duty Toggle Switch Series is our most robust series of toggle switches, available in several configurations of actuators and circuitries.

Web Resources

Download 2D print and technical resources at:
littelfuse.com/StandardHDToggleSwitches

Features and Benefits

- Silver contacts for corrosion resistance

Specifications Overview

Mounting:

Nickel Plated Brass Face Nut through
15/32 (11.90mm) Panel Hole
Part Number 5520: Black Finished
Face Nut

Voltage Ratings:

10A at 36V DC
15A at 24V DC
25A at 12V DC

Applications

- Construction Equipment
- Agricultural Equipment
- Material Handling Equipment
- Commercial Vehicles

Ordering Information

Please See Page 2 for Ordering Information

STANDARD HEAVY DUTY TOGGLE SWITCHES

Ordering Information

BULK PART NUMBER	BOXED PART NUMBER	BLISTER PART NUMBER	CIRCUITRY	HOUSING	ACTUATOR	POSITIONS	TERMINATION
5520	5520-BX	5520-BP	SPST	Plastic Bakelite with Plated Steel Cap	Standard handle: 11.94mm long	On-Off (Up-Down)	2 Screws
5582	5582-BX	5582-BP	SPST	Plastic with Plated Steel Cap	Standard handle: 17.46mm long	On-Off (Up-Down)	2 Screws
5584	5584-BX	—	SPDT	Plastic with Plated Steel Cap	Standard handle: 17.46mm long	On-On (Up-Down)	3 Screws
5586	5586-BX	5586-BP	SPDT	Plastic with Plated Steel Cap	Standard handle: 17.46mm long	On - Off - On (Up-Center-Down)	3 Screws
5588	5588-BX	5588-BP	DPST	Plastic with Plated Steel Cap	Standard handle: 17.46mm long	On-Off (Up-Down)	4 Screws
5590	5590-BX	—	DPDT	Plastic with Plated Steel Cap	Standard handle: 17.46mm long	On-On (Up-Down)	6 Screws
5592	5592-BX	5592-BP	DPDT	Plastic with Plated Steel Cap	Standard handle: 17.46mm long	On - Off - On (Up-Center-Down)	6 Screws
55014	55014-BX	55014-BP	SPST	Plastic with Plated Steel Cap	Standard handle: 17.46mm long	On - Of (Up-Down)	2 Blades
55016	55016-BX	—	SPDT	Plastic with Plated Steel Cap	Standard handle: 17.46mm long	On - Off - On (Up-Center-Down)	3 Blades
55017	55017-BX	—	DPST	Plastic with Plated Steel Cap	Standard handle: 17.46mm long	On - Off (Up-Down)	4 Blades
55018	55018-BX	—	DPDT	Plastic with Plated Steel Cap	Standard handle: 17.46mm long	On - On (Up-Down)	6 Blades
55019	55019-BX	55019-BP	DPDT	Plastic with Plated Steel Cap	Standard handle: 17.46mm long	On - Off - On (Up-Center-Down)	6 Blades
55020	55020-BX	55020-BP	SPST	Plastic with Plated Steel Cap	Standard handle: 17.46mm long	Off - Momentary On (Up-Down)	2 Screws
55021	55021-BX	55021-BP	SPDT	Black Plastic with Plated Steel Cap	Standard handle: 17.46mm long	Momentary On - Off - Momentary On (Up-Center-Down)	3 Screws
55036	55036-BX	—	SPDT	Plastic with Plated Steel Cap	Standard handle: 17.46mm long	On - Off - On (Up-Center-Down)	3 terminated 16AWG leads
55046	55046-BX	—	DPDT	Phenolic with Plated Steel Cap	Standard handle: 17.46mm long	Momentary On - Off - Momentary On (Up-Center-Down)	4 Blades
55054	55054-BX	55054-BP	DPDT	Plastic with Plated Steel Cap	Standard handle: 17.46mm long	Momentary On - Off - Momentary On (Up-Center-Down)	6 Screws
55088	55088-BX	55088-BP	SPDT	Plastic with Plated Steel Cap	Standard handle: 17.46mm long	On - Off - Momentary On (Up-Center-Down)	3 Screws
55020-04	55020-04-BX	55020-04-BP	SPST	Plastic with Plated Steel Cap	Standard handle: 17.46mm long	Momentary On - Off (Up-Down)	2 blunt-cut 16AWG leads
55021-07	55021-07-BX	55021-07-BP	SPDT	Weather-Resistant, PVC-Coated, Plasticized Housing	Standard handle: 17.46mm long	Momentary On - Off - Momentary On (Up-Center-Down)	3 blunt-cut 16AWG leads
55033-01	55033-01-BX	—	SPDT	Plastic with Plated Steel Cap	Standard handle: 17.46mm long	Momentary On - Off - Momentary On (Up-Center-Down)	3 Blades
55065-02	55065-02-BX	—	DPDT	Plastic with Plated Steel Cap	Long handle: 38.1mm long	Momentary On - Off - Momentary On (Up-Center-Down)	6 Blades
55065-03	55065-03-BX	—	DPDT	Plastic with Plated Steel Cap	Standard handle: 17.46mm long	Momentary On - Off - Momentary On (Up-Center-Down)	6 Blades
55107-01	55107-01-BX	—	4PDT	Black Plastic with Plated Steel Cap	Standard handle: 17.46mm long	On - On (Up-Down)	12 Blades
5582-10	5582-10-BX	5582-10-BP	SPST	Weather-Resistant, PVC-Coated, Plasticized Housing	Standard handle: 17.46mm long	On - Off (Up-Down)	2 blunt-cut 16AWG leads
5582-25	—	—	SPST	Hencol Sealed Plastic with Plated Steel Cap	Standard handle: 17.46mm long	On - Off (Up-Down)	2 stripped 16AWG leads
5582-27	—	—	SPST	Plastic with Boot Cap	Long handle: 25.4mm long	On - Off (Up-Down)	2-16AWG leads, terminated in Packard Connector #15300002
5582-30-BP	—	5582-30-BP	SPST	Hencol Sealed Plastic with Boot Cap	Long handle: 25.4mm long	On - Off (Up-Down)	2 stripped 16AWG leads