



RESISTANCE @ +25°C = 100,000 Ω ± 2%
 RESISTANCE/TEMPERATURE CURVE = "J"
 BETA "β" (0 TO +50°C) = 3,892°K NOMINAL
 TEMPERATURE COEFFICIENT @ +25°C = -4.4%/°C NOMINAL
 MAXIMUM TEMPERATURE RATING = +300°C

LEAD WIRE: 26 AWG, STRANDED CONDUCTOR, TWO CONDUCTOR,
 GLASS BRAID INSULATED, GLASS BRAID JACKETED CABLE,
 0.060" X 0.052" NOMINAL O.D.

*** ROHS COMPLIANT ***

SEE MANUFACTURING SPECIFICATION (LAYER 1)

"A"	CABLE LNGTH WAS 120"±6",+ROHS NOTE,TERMINALS & CONN (WAS STRIPPED 0.3" ± 0.2")	02/20/09	DD
NONE	RELEASE TO PRODUCTION	02/19/09	DD
REV	REVISION RECORD	DATE	APP

SCALE	NONE	U.S. SENSOR CORP. 1832 W. COLLINS AVE. ORANGE, CA. 92867 714-639-1000 www.ussensor.com THERMISTOR PROBE P/N USP9728
DRAWN BY	DAN DANKER	
DATE	02/19/09	
REV.	"A"	
LAYER	0 OF 2	