

# USP3986 Thermistor Probe




## Description

Littelfuse offers Stainless probe housings suitable for a wide range of temperature sensing applications. If the dimensions on this product won't work for your requirements, please contact us for further assistance.

## Features

- Temperature Standard
- Supplied with NIST Traceable Calibration Cert
- 105°C Max Operating Temperature


## Dimensions



Dimensions in inches.

A	B	C	D
0.250" ± 0.070" Strip	15.5" ± 1.0"	9.50" ± 0.500"	0.250" ± 0.005"

## Part Numbering System



**Note:** Not all combinations of Part Number codes are available. Contact Littelfuse for details.

## Specifications

Part Number	Resistance Ohms @25°C	R-T Curve	Temperature Coefficient (% / °C) @ 25°C	Beta (K) 0-50°C	Temperature Rating (°C)
USP3986	10000	J	- 4.4	3892	-55 to +105

**Disclaimer Notice** - Information furnished is believed to be accurate and reliable. However, users should independently evaluate the suitability of and test each product selected for their own applications. Littelfuse products are not designed for, and may not be used in, all applications. Read complete Disclaimer Notice at: [www.littelfuse.com/disclaimer-electronics](http://www.littelfuse.com/disclaimer-electronics)