



RESISTANCE @ +77°F (+25°C) = 2,000 Ω NOMINAL  
 ACCURACY (-15 TO +40°F) (-26.1 TO +4.4°C) = ± 3.0°F (± 1.67°C)  
 RESISTANCE/TEMPERATURE CURVE = "F"  
 BETA "β" (+32 TO +122°F) (0 TO +50°C) = 3,419°K NOMINAL  
 TEMPERATURE COEFFICIENT @ +77°F (+25°C) = -3.86%/°C NOMINAL  
 MAXIMUM OPERATING TEMPERATURE = +212°F (+100°C)

SEE MANUFACTURING SPECIFICATION (LAYER 1)

"A"	BASE RESISTANCE VALUE WAS 10,000 Ω	05/09/03	DD
NONE	RELEASE TO PRODUCTION	05/09/03	DD
REV	REVISION RECORD	DATE	APP

SCALE	NONE	<b>U.S. SENSOR CORP.</b> 1832 W. COLL INS AVE. ORANGE, CA . 92867 714-639-1000 www.ussensor.com
DRAWN BY	DAN DANKERT	
DATE	05/09/03	
REV.	"A"	
LAYER	0 OF 2	
		NTC THERMISTOR PROBE
		P/N USP4065