



RESISTANCE @ +25°C = 10,000 Ω ± 5%
 RESISTANCE/TEMPERATURE CURVE = "J"
 TEMPERATURE COEFFICIENT @ +25°C = -4.4%/°C NOMINAL
 BETA "β" (0 TO +50°C) = 3,892°K NOMINAL
 MAXIMUM TEMPERATURE RATING = +125°C

MOUNTING HOLE STUD SIZE = #4
 MOUNTING HOLE DIAMETER = 0.120" NOMINAL
 RING TONGUE STOCK THICKNESS = 0.040" NOMINAL

SEE MANUFACTURING SPECIFICATION (LAYER 1)

NONE	RELEASE TO PRODUCTION	11/17/05	DD
REV	REVISION RECORD	DATE	APP

SCALE	NONE	U.S. SENSOR CORP. 1832 W. COLL INS AVE. ORANGE, CA . 92867 714-639-1000 www.ussensor.com
DRAWN BY	DAN DANKERT	
DATE	11/17/05	THERMISTOR PROBE
REV.	NONE	P/N USP6295
LAYER	0 OF 2	