



RESISTANCE @ +25°C = 10,000 Ω NOMINAL  
 ACCURACY (+60 TO +100°C) = ± 5.0°C  
 RESISTANCE/TEMPERATURE CURVE = "J"  
 TEMPERATURE COEFFICIENT @ +25°C = -4.4%/°C NOMINAL  
 BETA "β" (0 TO +50°C) = 3,892°K NOMINAL  
 MAXIMUM TEMPERATURE RATING = +135°C

MOUNTING HOLE DIAMETER = 0.145" NOMINAL  
 MOUNTING HOLE STUD SIZE = #6

SEE MANUFACTURING SPECIFICATION (LAYER 1)

NONE	RELEASE TO PRODUCTION	02/07/07	DD
REV	REVISION RECORD	DATE	APP

SCALE	NONE	<b>U.S. SENSOR CORP.</b> 1832 W. COLLINS AVE. ORANGE, CA 92867 714-639-1000 www.ussensor.com
DRAWN BY	DAN DANKERT	
DATE	02/07/07	
REV.	NONE	
LAYER	0 OF 2	
		<b>THERMISTOR PROBE</b>
		<b>P/N USP7570</b>