



RESISTANCE @ +25°C = 10,000 Ω ± 1%
 RESISTANCE/TEMPERATURE CURVE= "J"
 TEMPERATURE COEFFICIENT @ +25°C = -4.4%/°C NOMINAL
 BETA "β" (0 TO +50°C) = 3,892°K NOMINAL
 MAXIMUM TEMPERATURE RATING = +125°C

LEAD WIRE: 30 AWG (0.010" DIAMETER), SINGLE CONDUCTOR,
 SOLID CONDUCTOR, KYNAR INSULATED

*** ROHS COMPLIANT ***

SEE MANUFACTURING SPECIFICATION (LAYER 1)

NONE	RELEASE TO PRODUCTION	01/11/12	DD
REV	REVISION RECORD	DATE	APP

SCALE NONE	© COPYRIGHT U.S. SENSOR CORP. 714-639-1000 www.ussensor.com THERMISTOR PROBE P/N USP12840
DRAWN BY DAN DANKERT	
DATE 01/11/12	
REV NONE	
LAYER 0 OF 2	