



- NOTES:
 1. HOLDER MATERIAL : PVC NATURAL COLOR.
 2. WIRE : 1015 12AWG RED.
 3. RATING : MAX. 30A, 32VDC.
 4. FUSEHOLDERS SHOULD NOT BE PLACED UNDER TENSION IN FINAL APPLICATION

METRIC
ASSEMBLY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN BRACKETS [] ARE INCHES
 UNLESS OTHERWISE SPECIFIED, DIMENSIONS DO NOT INCLUDE PLATING.
 © DENOTES CRITICAL CHARACTERISTICS.
 CPK DENOTES CPK DIMENSIONS, -MINIMUM CPK VALUE
 ST DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS
 CP DENOTES CP DIMENSIONS, -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE

| | | | | |
|----|--------------|-------------|-------|-----|
| NO | COMPONENT NO | DESCRIPTION | QTY/M | U/M |
| - | - | - | - | - |
| - | - | - | - | - |
| - | - | - | - | - |

| COPIES TO | | MATL SPEC | | REVISION | | CHK | | APD | | |
|--|----|-------------|---------------|----------|----------|-------------------------|----------|-----------|--|--|
| 1 | 9 | 18 | SEE NOTES | A | 05/10/12 | 504880ERA-RELEASED FYUE | | | | |
| 2 | 10 | 19 | FINISH N/A | | | | | | | |
| 3 | 12 | 20 | | | | | | | | |
| 4 | 13 | 21 | | DRW | DATE | 05/02/12 | SCALE | 1:1 | | |
| 5 | 14 | 23 | | CHK | DATE | | SUPER DR | | | |
| 6 | 15 | 33 | | DATE | | FINISH GOOD WT | | | | |
| 7 | 16 | 43 | | APPD | | | | | | |
| 8 | 17 | 53 | | | | | | | | |
| TOLERANCES UNLESS OTHERWISE SPECIFIED (REF. ISO 2768-fH) | | GRAMS/PIECE | | | | | | | | |
| DIMENSION | | UP TO | | OVER | | UP TO | | OVER | | |
| 0.5 - 3 | | 3 - 6 | | 6 - 30 | | 30 - 120 | | 120 - 400 | | |
| TOLERANCE | | ±0.05 | | ±0.1 | | ±0.15 | | ±0.2 | | |
| 3RD ANGLE PROJECTION | | | | | | | | | | |
| TITLE ATO FUSE HOLDER (SMART GLOW) | | | | | | | | | | |
| REVISION DRWG. NO. A OL-0FHA0001HXGLO | | | | | | | | | | |
| LITTELFUSE DES PLAINES, ILLINOIS 60016 | | | | | | | | | | |