




THIS DRAWING AND THE INFORMATION CONTAINED WITHIN IT ARE CONFIDENTIAL AND MAY NOT BE COPIED OR DISCLOSED WITHOUT THE WRITTEN PERMISSION OF LITTELFUSE.

PART NUMBER	"A"	"B"	"C"	"D"	WIRE TYPE
OFHA0001ZXJ-GRN	101.6±5	101.6±5	6.35±2	6.35±2	16 AWG GPT WIRE

REVISIONS				
ZONE	REV.	DESCRIPTION	DATE	APPROVED
	A	PCO #5300031. INITIAL RELEASE. DSILVA	3/7/2022	S.CASTILLO




SECTION A-A

- NOTES:
- MATERIAL:
 - HOLDER: PVC, COLOR BLACK.
 - CONTACTS: COPPER ALLOY, TIN PLATED.
 - RATING: MAX 20A, 32 VDC

NO.	COMPONENT NO.	COMPONENT NAME	QTY	U	
TOLERANCES UNLESS OTHERWISE SPECIFIED (REF ISO 2768-FH)					
.5 to 3	>3 to 6	>6 to 30	>30 to 120	>120 to 400	ANGLE
±0.05	±0.05	±0.10	±0.15	±0.2	NONE

DIMENSIONS ARE SHOWN IN MILLIMETERS. DIMENSIONS AND TOLERANCES ARE DEFINED ACCORDING TO ANSI/ASME Y14.5-1994.

PER CHI-NP020-0008 PROCEDURE	SYMBOL	DESCRIPTION
●	FIT/ FUNCTION CRITICAL CHARACTERISTICS	
<S>	SAFETY/ COMPLIANCE CRITICAL CHARACTERISTICS SYMBOL	
CPK	DENOTES CPK DIMENSIONS MINIMUM CPK VALUE	
ST	DENOTES A CHARACTERISTIC THAT PROVIDES AN INDICATION OF PROCESS PERFORMANCE. PROCEDURE FOR MEASUREMENT AND TRACKING TO BE DEFINED IN LITTELFUSE INSPECTION INSTRUCTIONS	
CP	DENOTES CP DIMENSIONS. -MINIMUM CP VALUE MUST BE WITHIN THE DIMENSIONAL LIMITATIONS SHOWN ON DRAWING AND INITIALLY LOCATED TO ALLOW FOR MAXIMUM TOOL LIFE	

<table border="1"> <thead> <tr> <th>NAME</th> <th>DATE</th> </tr> </thead> <tbody> <tr> <td>DRAWN DSILVA</td> <td>2/28/2022</td> </tr> <tr> <td>CHECKED S.CASTILLO</td> <td>3/7/2022</td> </tr> </tbody> </table>	NAME	DATE	DRAWN DSILVA	2/28/2022	CHECKED S.CASTILLO	3/7/2022	 <p>Expertise Applied Answers Delivered</p>			
NAME	DATE									
DRAWN DSILVA	2/28/2022									
CHECKED S.CASTILLO	3/7/2022									
<table border="1"> <tr> <td>FORM NO: CVP-PE40-0003 REV B</td> <td>TITLE</td> </tr> <tr> <td>THIRD ANGLE PROJECTION</td> <td>AUTOFUSE HOLDER IN-LINE</td> </tr> </table>	FORM NO: CVP-PE40-0003 REV B	TITLE	THIRD ANGLE PROJECTION	AUTOFUSE HOLDER IN-LINE						
FORM NO: CVP-PE40-0003 REV B	TITLE									
THIRD ANGLE PROJECTION	AUTOFUSE HOLDER IN-LINE									
<table border="1"> <tr> <td>DO NOT SCALE DRAWING</td> <td>SCALE 1:1</td> <td>SHEET 1 OF 1</td> </tr> </table>	DO NOT SCALE DRAWING	SCALE 1:1	SHEET 1 OF 1	<table border="1"> <tr> <th>SIZE</th> <th>DWG. NO.</th> <th>REV.</th> </tr> <tr> <td>B</td> <td>OUTLINE OL-0FHA0001ZXJ-GRN</td> <td>A</td> </tr> </table>	SIZE	DWG. NO.	REV.	B	OUTLINE OL-0FHA0001ZXJ-GRN	A
DO NOT SCALE DRAWING	SCALE 1:1	SHEET 1 OF 1								
SIZE	DWG. NO.	REV.								
B	OUTLINE OL-0FHA0001ZXJ-GRN	A								